

# Full-spectrum Quantum Sensor | SQ-521-SS and SQ-522-SS - Digital Outputs

Quantum sensor with an improved spectral response providing accurate PAR (PPFD) measurements under all light sources, including LEDs.

## Refined Spectral Response

Improved spectral response increases the accuracy of LED measurements making it ideal for use with both natural and electric light sources.

## Accurate, Stable Measurements

Calibration in controlled laboratory conditions is traceable to an NIST lamp. Quantum sensors are cosine-corrected, with directional errors less than  $\pm 5\%$  at a solar zenith angle of  $75^\circ$ . Long-term non-stability determined from multiple replicate quantum sensors in accelerated aging tests and field conditions is less than 2% per year.

## Rugged, Self-cleaning Housing

Patented domed shaped sensor head (diffuser and body) facilitate runoff of dew and rain to keep the sensor clean and minimize errors caused by dust blocking the radiation path. Sensors are housed in rugged anodized aluminum body and electronics are fully potted.

## Output Options


Digital output options include SDI-12 and ModBus communication protocol. Sensor is also available in multiple analog output options, attached to a hand-held meter with digital readout, and as a 'digital' smart sensor that uses USB communication and custom software to interface directly to a computer.

## Typical Applications

PPFD measurement over plant canopies in outdoor environments, greenhouses, and growth chambers, and reflected or under-canopy (transmitted) PPFD measurements in the same environments. Quantum sensors are also used to measure PPFD in aquatic environments, including salt water aquariums where corals are grown.




## Cosine Response



Mean cosine response of seven Apogee SQ-500 quantum sensors. Cosine response measurements were made on the rooftop of the Apogee building in Logan, UT. Cosine response was calculated as the relative difference of SQ-500 quantum sensors from the mean of replicate reference quantum sensors (LI-COR models LI-190 and LI-190R, Kipp & Zonen model PQS 1). The red data are AM measurements; the green data are PM measurements.

## Spectral Response



Mean spectral response measurements of six replicate Apogee SQ-100 and SQ-500 series quantum sensors. Spectral response measurements were made at 10 nm increments across a wavelength range of 300 to 800 nm in a monochromator with an attached electric light source. Measured spectral data from each quantum sensor were normalized by the measured spectral response of the monochromator/electric light combination, which was measured with a spectroradiometer.

## Spectral Errors of Commercial Quantum Sensors


Radiation Source	Apogee SQ-500	Apogee SQ-110 SQ-120	LI-COR LI-190	Kipp & Zonen PQS 1
Sun (Clear Sky)	-2.2	0.0	-0.4	-1.0
Sun (Cloudy Sky)	-1.7	1.4	-0.2	-1.3
Sun (Reflected from Deciduous Leaves)	-2.0	4.9	-0.8	1.1
Sun (Transmitted below Wheat Canopy)	-1.1	6.4	-0.1	-0.3
Cool White Fluorescent (T5)	0.0	0.0	0.0	0.0
Metal Halide	0.9	-3.7	0.2	-1.7
Ceramic Metal Halide	-0.3	-6.0	0.4	-0.7
High Pressure Sodium	0.0	0.8	1.3	1.4
Red/Blue LED (16 % 444 nm, 84 % 667 nm peaks)	-3.4	-65.3	3.5	-1.8
Red/White LED (6.5 % 436 nm, 4.5 % 531 nm, 89 % 668 nm peaks)	-3.0	-60.3	2.6	-1.7

Spectral errors are theoretical errors calculated from sensor spectral responses (Apogee SQ-100 and SQ-500 series shown in graph above) and spectral output of radiation sources (measured with a spectroradiometer). Only spectral errors are listed in the table. Calibration, cosine, and temperature error can also contribute to measurement error.

## Calibration Traceability

Apogee Instruments SQ-500 series quantum sensors are calibrated through side-by-side comparison to the mean of four Apogee model SQ-500 transfer standard quantum sensors under high output T5 cool white fluorescent lamps. The transfer standard quantum sensors are calibrated through side-by-side comparison to the mean of at least three LI-COR model LI-190R reference quantum sensors under high output T5 cool white fluorescent lamps. The reference quantum sensors are recalibrated on a biannual schedule with a LI-COR model 1800-02 and quartz halogen lamp that are traceable to the National Institute of Standards and Technology (NIST).

## Dimensions



### SQ-521-SS

### SQ-522-SS

Input Voltage Requirement	4.5 to 24 V DC	
Current Drain	0.6 mA (quiescent), 1.3 mA (active)	12.5 mA (quiescent), 13.5 mA (active)
Calibration Uncertainty	± 5 % (see Calibration Traceability above)	
Output Range	0 to 40 mV	
Measurement Range	0 to 4000 $\mu\text{mol m}^{-2} \text{s}^{-1}$	
Measurement Repeatability	Less than 0.5 %	
Long-term Drift (Non-stability)	Less than 2 % per year	
Non-linearity	Less than 1 % (up to 4000 $\mu\text{mol m}^{-2} \text{s}^{-1}$ )	
Response Time	0.6 s, time for detector signal to reach 95 % following a step change; fastest data transmission rate for SDI-12 circuitry is 1 s	320 ms
Field of View	180°	
Spectral Range	389 to 692 nm ± 5 nm (wavelengths where response is greater than 50% of maximum)	
Spectral Selectivity	Less than 10 % from 412 to 682 nm ± 5 nm	
Directional (Cosine) Response	± 5 % at 75° zenith angle	
Azimuth Error	Less than 0.5 %	
Tilt Error	Less than 0.5 %	
Temperature Response	-0.11 ± 0.03 % per C	
Uncertainty in Daily Total	Less than 5 %	
Detector	Blue-enhanced silicon photodiode	
Housing	Anodized aluminum body with acrylic diffuser	
IP Rating	IP68	
Operating Environment	-40 to 70 C; 0 to 100 % relative humidity; can be submerged in water up to depths of 30 m	
Dimensions	45.0 mm height, 23.5 mm diameter	
Mass	100 g	
Cable	5 m of shielded, twisted-pair wire; additional cable available in multiples of 5 m; santoprene rubber jacket (high water resistance, high UV stability, flexibility in cold conditions); pigtail lead wires	
Warranty	4 years against defects in materials and workmanship	